
Reference Electro Lift M-12475-A



30 29 28	DM7019 M1322P2	1	BEARING, BALL, 6206ZZ, 1.18 ID, 2.44 □D, .62 W  SEE N□TE D  C□VER, SPUR GEAR, BC-3P SEE N□TE #14  PINION, J□B SPECIFIC SEE N□TE #13		EE NOTE SHEET		14 & KIT NOTES A-E  ELECTROLIFT		
27	DM7018	1	BEARING, BALL, 6211ZZ, 2.16 ID, 3.93 □D, .82 W  SEE N□TE D	55	DM7335	1	BEARING, BALL, 6216ZZ, 3.14ID,5.51□D,1.02W SEE N□TE D  Customer Service 1-800-338-9951		
26	FS129	6	SCREW,HHCS,3/8-16×1 SEE N□TE A		N / A				
25	M1310A	1	COVER, SIDE, GEAR CASE, BC	54	N/A	_			
24	K10755	1	KIT, SHIM, B-HOIST, SIDE COVER	53	K1963A1P1	1	COVER, BALL BRG		
23	DM7010	1	BEARING, TRB, CUP, 4.25 □D SEE N□TE B	52	FS124	10	SCREW,HHCS,5/16-18×1-1/4   SEE N□TE E		
22	DM7009	1	BEARING, TRB, CONE, 2.25 ID    SEE N□TE B	51	K900P11	1	COVER, BALL BRG		
21	K1670	1	SHAFT, PINION, BC-3P	50	DM7031	1	SEAL, SHAFT, 2.25 ID, 3.35 □D SEE N□TE C		
20		1	WORM WHEEL, JOB SPECIFIC SEE NOTE #5	49	FS370	2	PIN, ROLL, 1/2×1-1/2 SEE NOTE #14		
19	DM7003	1	BEARING, TRB, CONE, 1.50 ID ⊗SEE NOTE B	48	K10849P3	1	KEY, 5/16x5/16,2-15/16		
18	DM7004	1	BEARING, TRB, CUP 3.00 □D SEE N□TE B	47A	FS333	2	PIPEPLUG,1/2 SQHD CORED   SEE NOTE		
17	M2959E	1	ADAPTER, MOTOR, T477, C FACE,BASE & FLR MTD	47	FS333	1	PIPEPLUG,1/2 SQHD CORED SEE NOTE		
16	N/A	-		46	K10910P2	1	KEY,1/2×1/2×2		
15	N/A	-		45	K10910P4	1	KEY,1/2×1/2×1-15/16		
14	FS320	4	WASHER,INT.TOOTH,1/2,PLATED ⊠SEE NOTE A	44a	FS312	7	WASHER,L,5/16		
13	FS207	4	SCREW,SHCS,1/2-13×1-1/4 SEE N□TE A	44	FS127	7	SCREW,HHCS,5/16-18×2-1/4 SEE N□TE A		
12	K122P2	1	SLEE∨E, MOTOR SHAFT, B HOIST	43	M1324AP2	1	PLATE, SIDE, BC3P-BM SEE NOTE #14		
11	DM7030	1	SEAL, SHAFT, 1.18 ID, 2.06 □D SEE N□TE C	42		1	GEAR, JOB SPECIFIC SEE NOTE #13		
10	T477BC	1	GEAR CASE, BC HOIST	41		1	DRUM SHAFT, JOB SPECIFIC		
	FS337	1	PIPEPLUG,1/2 SQHD CORED, W/STRAIGHT VENT	40	K10858P3	1	KEY, 3/4×3/4×3		
9		_		39	K10858P4	1	KEY, 3/4, BC 3P BASE MTD, GEAR		
8	FS336	1	PIPEPLUG,1/8 SQHD, S□LID SEE N□TE A	38	FS216	1	SOCKET HEAD SET SCREW,1/2-13x1/2,KNURLED		
		1		37		1	DRUM, JOB SPECIFIC		
7		1	WORM SHAFT, JOB SPECIFIC SEE NOTE #5	36	FS315	10	WASHER,L,3/8,PLAIN SEE NOTE #1		
6	DM7005	2	BEARING, TRB, CONE, 1.25 ID SEE NOTE B	35	FS131	10	SCREW,HHCS,3/8-16×1-1/2 SEE NOTE		
5	DM7006	2	BEARING, TRB, CUP, 3.125 □D SEE N□TE B	34	DM7020	1	BEARING, BALL, 6212ZZ, 2.36ID,4.33□D,.86W SEE N□TE I		
4	K10756	1	KIT, SHIM, B-HOIST, END COVER	33	FS123	4	SCREW,HHCS,5/16-18×1 , GR2		
3	K123	1	COVER, END, GEAR CASE, B	32		1.4	WASHER,L,5/16, PLAIN SEE NOTE		
2	FS315	10	WASHER,L,3/8 ⊠SEE N□TE A		FS312	14			
1	FS130	4	SCREW,HHCS,3/8-16×1-1/4 SEE N□TE A	31	K900AP30	1	COVER, BALL BRG BC-3P Base Mounted Gearcase Assembly		
ITEM #	PART #	QTY	DESCRIPTION	ITEM #	PART #	QTY	DESCRIPTION Parts List		
BILL OF MATERIALS Sheet 2 of 3									

## NOTES:

- 1) \* APPLY ANTISEIZE COMPOUND
- 2)♦ SEE LAST SHEET FOR LOCTITE SEALANT AND GASKET APPLICATION INSTRUCTIONS.
- 3) @ APPLY BLUE TYPE THREADLOCK COMPOUND, TORQUE TO 24 FT-LBS
- 4) USE THE SAME AMOUNT AND COLOR OF SHIMS AS ORIGINAL SET.
- 5) IDENTIFICATION CHART


NO OF TEETH	WORM WHEEL P/N	WORM SHAFT P/N
36	M336A	M320
41	M12207A	M2851
67	M2864A	M2853

- 6) DIL CAPACITY 20 DZ. EXXON CYLESSTIC TK680 OR EQUIV. E/L P/N DM7146 DR MDBIL SHC 634 DR EQUIV. (SYNTHETIC) E/L P/N DM7381
- 7) PRESS ITEM 20 ONTO ITEM 21 CENTRALLY LOCATED ON ITEM 45
- 8) PRESS ITEM INTO MATING HOUSING OR COVER
- 9) TO BE PRESSED ON MATING SHAFT
- 10) TAP WITH MALLET AFTER PRESSING ITEM 5
- 11) PRESS ITEM 42 ONTO ITEM 41 CENTRALLY LOCATED ON ITEM 40
- 12) COAT ALL TEETH WITH EXXON RONEX MP GREASE P/N DM7154
  ITEM 29 IS TO BE AT APPROX. 50% CAPACITY FULL OF GREASE WHEN SEALED.
- 13) IDENTIFICATION CHART

PINION- THE SMALLER OF THE TWO GEARS
GEAR- THE LARGER GEAR
PINIONS AND GEARS ARE MATCHED SETS AS KITS

KIT	# TEETH	PINION P/N	# TEETH	GEAR P/N
K11202P1	12	K1636P10	51	K1636P11
K11202P2	13	K1636P3	50	K1636P18
K11202P3	14	K1636P16	49	K1636AP34
K11202P4	15	K1636P12	48	K1636AP38
K11202P5	16	K1636P14	47	K1636P27
K11202P6	17	K1636P28	46	K1636AP32
K11202P7	18	K1636P24	45	K1636AP37
K11202P8	19	K1636AP30	44	K1636AP35
K11202P9	20	K1636P25	43	K1636AP39
K11202P10	21	K1636P19	42	K1636P20

14) M1322P2 & M12617 ARE NOT AVAILABLE INDIVIDUALLY. THEY ARE AVAILABLE ONLY AS MATCHED SET M12274A, ALONG WITH NOTED HARDWARE.



ELECTRULIFT

A) THIS PART CAN ONLY BE ORDERED AS PART OF GEARCASE HARDWARE KIT #K11236.

- B) THIS PART CAN ONLY BE ORDERED AS PART OF GEARCASE BEARING KIT #K11158.
- C) THIS PART CAN ONLY BE ORDERED AS PART OF SEAL KIT #K11159.
- D) THIS PART CAN ONLY BE ORDERED AS PART OF SPUR GEARBOX BEARING KIT #K11288.
- E) THIS PART CAN ONLY BE ORDERED AS PART OF SPUR GEARBOX HARDWARE KIT #K11237B.
- F) FOR BOTH SEALS & SHIMS, ORDER SEAL & SHIM KIT #K11282.

BC-3P Base Mounted Gearcase Assembly Parts List Sheet 3 of 3

## Type 'A', 'B', and 'BC' Hoist Gearbox

## Notes:

- 1. Required components: 518 Gasket Eliminator, 565 Pipe Sealant, 598 RTV, and 7649 Primer
- 1. All metal surfaces to be cleaned with brake cleaner, acetone, or Loctite Cleaner/Degreaser. After cleaning, all surfaces will be wiped down and dried.
- 2. All Loctite sealants, retaining compounds, and gasket eliminators require 3 hours to set and 24 hours to fully cure. None of these materials should come into contact with oil or grease before this time.

Issue 1, 5/28/15

4. Apply 518 Gasket Eliminator in a continuous bead, circling each bolt hole as shown. Do not spread.













Note:

Spray both sides of the shim 'stack' with Loctite 7649 Primer. There is no need to spray each shim individually.



