
Service Bulletin Sheets B-Single Drum Opp GLS Iss. 7: 6/10/15

Reference Electro Lift M-12439-A



33	DM7003	2	BEARING, TRB, CONE, 1.50 ID	⊗SEE	NDTE	
32	DM7004	2	BEARING, TRB, CUP, 3.00 DD	⊗SEE	NOTE	
31	FS333	1	PIPEPLUG,1/2 SQHD CORED,CI PLAIN	⊗SEE	NOTE	. 1
30	FS127	7	SCREW,HHCS,5/16-18x2-1/4, GR2,PLAIN	⊗SEE	NOTE	. 1
29	FS312	7	WASHER,L,5/16, PLAIN	⊗SEE	NDTE	
28		1	DRUM SHAFT, JOB SPECIFIC			
27	K10849P5	1	KEY, 5/16×5/16, 2, A:B DRUM SHAFT			
26	K10924P1	1	KEY, 3/8x3/8, 1-7/8, B, WORM WHEEL			
25		1	WORM WHEEL, SEE NOTE #5			
24	DM7028	2	SEAL,SHAFT,1.5 ID, 2.37 DD	⊠SEE	NOTE	
23	FS129	6	SCREW,HHCS,3/8-16x1,GR2,PLAIN	⊗SEE	NDTE	
22	M323	1	COVER, SIDE, GEAR CASE,B			
21	FS445	1	SUCKET HEAD SET SCREW 3/8-16x1/2, KNURLED			
20	K10755	1	KIT, SHIM, B-HOIST, SIDE COVER			
19		1	DRUM, JOB SPECIFIC			
18	N/A	_	-			
17	N/A	-	-			
16	M2959	1	ADAPTER, MOTOR, T477, C FACE			
15	FS320	4	WASHER,INT.TOOTH,1/2,PLATED	⊠SEE	NOTE	4
14	FS207	4	SCREW, SHCS, 1/2-13x1-1/4	⊠SEE	NOTE	4
13	K122P2	1	SLEEVE, MOTOR SHAFT, B HOIST			
12	DM7030	1	SEAL, SHAFT, 1.18 ID, 2.06 OD	⊠SEE	NOTE	(
11	M12142	1	GEAR CASE, B HOIST, GLS			
10	FS337	1	PIPEPLUG,1/2 SQHD CORED, W/STRAIGHT VENT	⊠SEE	NOTE	4
9	FS336	1	PIPEPLUG,1/8 SQHD,CAST IRON, SOLID	⊗SEE	NOTE	1
8	K10849P3	1	KEY, 5/16×5/16, 2-15/16			
7		1	WORM SHAFT, SEE NOTE #5			
6	DM7005	2	BEARING, TRB, CONE, 1.25 OD	⊗SEE	NOTE]
5	DM7006	2	BEARING, TRB, CUP, 3.125 0D	≫SEE		-
4	K10756	1	KIT, SHIM, B-HOIST, END COVER			
3	K123	1	COVER, END, GEAR CASE, B			
2	FS315	10	WASHER,L,3/8, PLAIN	⊗SEE	NOTE	-
1	FS130	4	SCREW,HHCS,3/8-16×1-1/4,GR2,PLAIN	⊠SEE		
						_

NOTES:

- 1) * APPLY ANTISEIZE COMPOUND
- 2) ♦ SEE LAST SHEET FOR LOCTITE SEALANT AND GASKET APPLICATION INSTRUCTIONS.
- 3) P APPLY BLUE TYPE
 THREADLOCK COMPOUND,
 TORQUE TO 24 FT-LBS



- 4) USE THE SAME AMOUNT AND COLOR OF SHIMS AS ORIGINAL SET.
- 5) IDENTIFICATION CHART

NO OF TEETH	WORM WHEEL P/N	WORM SHAFT P/N		
36	M321A	M320		
41	M2852A	M2851		
67	M2854A	M2853		

- 6) DIL CAPACITY 20 DZ.

 EXXON CYLESSTIC TK680 DR EQUIV. E/L P/N DM7146

 DR MDBIL SHC 634 DR EQUIV. (SYNTHETIC) E/L P/N DM7381
- 7) PRESS ITEM 25 ONTO ITEM 28 CENTRALLY LOCATED ON ITEM 26
- 8) PRESS ITEM INTO MATING HOUSING OR COVER
- 9) TO BE PRESSED ON MATING SHAFT
- 10) TAP WITH MALLET AFTER PRESSING ITEM 5
- A) THIS PART CAN ONLY BE ORDERED AS PART OF GEARCASE HARDWARE KIT #K11236.
- B) THIS PART CAN ONLY BE ORDERED AS PART OF GEARCASE BEARING KIT #K11155.
- C) THIS PART CAN ONLY BE ORDERED AS PART OF SEAL KIT #K11157.
- D) FOR BOTH SEALS & SHIMS, ORDER SEAL & SHIM KIT #K11281.

B-Single Hook GLS on Opposite Std Side Gearcase Parts List Sheet 2 of 2


Type 'A', 'B', and 'BC' Hoist Gearbox

Notes:

- 1. Required components: 518 Gasket Eliminator, 565 Pipe Sealant, 598 RTV, and 7649 Primer
- 1. All metal surfaces to be cleaned with brake cleaner, acetone, or Loctite Cleaner/Degreaser. After cleaning, all surfaces will be wiped down and dried.
- 2. All Loctite sealants, retaining compounds, and gasket eliminators require 3 hours to set and 24 hours to fully cure. None of these materials should come into contact with oil or grease before this time.

Issue 1, 5/28/15

4. Apply 518 Gasket Eliminator in a continuous bead, circling each bolt hole as shown. Do not spread.













Note:

Spray both sides of the shim 'stack' with Loctite 7649 Primer.
There is no need to spray each shim individually.



